




Advanced pellicle for 32nm/22nm immersion technologies with high NA membrane

MLI's 801 pellicle



- Super thin film for optical improvement
- Optimized film to achieve highest transmission of $\geq 99\%$ @193nm from 0 to 20 degree incident angle.
- Available with low stand-off frame to increase inspection area and reduce flatness influence post mounting
- Minimum adhesive residue post mount
- MLI's 801 advanced pellicle comes with the lowest outgassing packaging material available

Contact your local Sales Representative or MLI today for details and samples of MLI's new advanced DUV pellicles.